

Eaton 723624-4FSQT

Catalog Number: 723624-4FSQT

Eaton B-Line series ground mounted panel enclosure, 72" height, 24" length, 36" width, NEMA 4, Hinged cover, 4FSQT enclosure, Ground mount, Large single door, No mounting provisions, Carbon steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 4 panel enclosures	723624-4FSQT
	UPC
	782051894653
Product Length/Depth	Product Height
24 in	72 in
Product Width	Product Weight
36 in	335.7 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Product specifications

Special features

1/4 turn latches

Closure type

Hinged

Finish color

Painted

Color

ANSI 61 gray

Wall thickness

12 gauge, 14 gauge

Material

Carbon steel

Mounting method

Ground

Country of origin

US

Cover type

Hinged

Mounting hole details

No mounting provisions

Locking provisions

Padlock provision

NEMA Rating

4

Model

4FSQT enclosure

Style

Large single door

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 723624-4FSQT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)