

Eaton 723624-4XSFSDA3PT

Catalog Number: 723624-4XSFSDA3PT

Eaton B-Line series ground mounted panel enclosure,72" height,36" length,36" width,NEMA 4X,Hinged cover,4XSFSDA3PT enclosure,Ground mount,Large single door,No mounting provisions,304 stainless,Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 4X panel enclosures	723624-4XSFSDA3PT
	UPC
	782051892550
Product Length/Depth	Product Height
36 in	72 in
Product Width	Product Weight
36 in	423.4 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

304 stainless steel

Wall thickness

12 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Large single door

Model

4XSFDA3PT enclosure

Cover type

Hinged

Mounting method

Ground

Mounting hole details

No mounting provisions

Locking provisions

Key lock padlock provision

Closure type

Hinged

Special features

3-pt latching handle

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 723624-4XSFDA3PT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)