

Eaton 726018-4XSFDQT

Catalog Number: 726018-4XSFDQT

Eaton B-Line series ground mounted panel enclosure, 72" height, 18" length, 60" width, NEMA 4X, Hinged cover, 4XSFDQT enclosure, Ground mount, Large double door, Ground mount legs, 304 stainless steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 4X panel enclosures	726018-4XSFDQT
	UPC
	782051894585
Product Length/Depth	Product Height
18 in	72 in
Product Width	Product Weight
60 in	507.1 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Product specifications

Special features

1/4 turn latches

Closure type

Hinged

Finish color

#4 brushed

Color

Gray

Wall thickness

12 gauge, 14 gauge

Material

304 stainless steel

Mounting method

Ground

Country of origin

US

Cover type

Hinged

Mounting hole details

Ground mount legs

Locking provisions

Padlock provision

NEMA Rating

4X

Model

4XSFDQT enclosure

Style

Large double door

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 726018-4XSFDQT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)