

Eaton 884-4QT

Catalog Number: 884-4QT

Eaton B-Line series JIC panel enclosure, 8" height, 4" length, 8" width, NEMA 4, Hinged cover, 4QT enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	884-4QT
UPC	Product Length/Depth
782051881721	4 in
Product Height	Product Width
8 in	8 in
Product Weight	Certifications
7.7 lb	UL 50
	CSA C22.2.
	NEMA

Product specifications

Special features

Continous piano hinge,panel mount,1/4 turn latches

Closure type

Hinged

Finish color

Painted

Color

ANSI 61 gray

Wall thickness

16 gauge

Material

Carbon steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

External mounting feet

NEMA Rating

4

Model

4QT enclosure

Style

Small single door

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 884-4QT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)