

Eaton AC-1236B

Catalog Number: AC-1236B

Eaton B-Line series console enclosures and accessories, 36" height, 24" length, 36" width, NEMA 12, Hinged cover, AC-12 console, Ground mount, Medium single door, No mounting provisions, Carbon steel, Oil-resistant gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series console enclosures and accessories	AC-1236B
	UPC
	782051425062
Product Length/Depth	Product Height
24 in	36 in
Product Width	Product Weight
36 in	157.1 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

AC-12 console

Cover type

Hinged

Mounting method

Ground

Mounting hole details

No mounting provisions

Locking provisions

Key locking

Closure type

Hinged

Special features

3-pt latching handle, plated screws

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - AC-1236B](#)