

Eaton AC-12C12SS

Catalog Number: AC-12C12SS

Eaton B-Line series consolelet enclosures, 12" height, 9.12" length, 12" width, NEMA 12, Screw cover, ACSS conolet, Surface mounted, Medium single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications

Product Name	Catalog Number
Eaton B-Line series consolelet enclosures	AC-12C12SS
UPC	Product Length/Depth
782051140903	9.12 in
Product Height	Product Width
12 in	12 in
Product Weight	Certifications
13.6 lb	UL 508A
	CSA C22.2.
	NEMA

Product specifications

Special features

Stainless screws

Closure type

Continous hinge

Finish color

#4 brushed

Color

Gray

Wall thickness

14 gauge

Material

304 stainless steel

Mounting method

Surface

Country of origin

US

Cover type

Screw

Mounting hole details

External mounting feet

NEMA Rating

12

Model

ACSS consolet

Style

Medium single door

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - AC-12C12SS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)