

# Eaton AC-16C24

Catalog Number: AC-16C24

Eaton B-Line series consolelet enclosures, 16" height, 11.12" length, 20" width, NEMA 12, Hinged cover, AC conolet, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket

## General specifications



Product Name	Catalog Number
Eaton B-Line series consolelet enclosures	AC-16C24
UPC	Product Length/Depth
782051410129	11.12 in
Product Height	Product Width
16 in	20 in
Product Weight	Certifications
29.2 lb	UL 508A
	CSA C22.2.
	NEMA

## Product specifications

### Special features

Continuous hinge, plated screws

### Closure type

Hinged

### Finish color

Painted

### Color

ANSI 61 gray

### Wall thickness

14 gauge

### Material

Carbon steel

### Mounting method

Surface

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

External mounting feet

### NEMA Rating

12

### Model

AC console

### Style

Medium single door

## Resources

### Catalogs

[Pushbutton-enclosure-operator.pdf](#)

### Specifications and datasheets

[Eaton Specification Sheet - AC-16C24](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)