

Eaton AC-16C30

Catalog Number: AC-16C30

Eaton B-Line series console enclosures, 16" height, 11.12" length, 30" width, NEMA 12, Hinged cover, AC conolet, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series console enclosures	AC-16C30
UPC	Product Length/Depth
782051410143	11.12 in
Product Height	Product Width
16 in	30 in
Product Weight	Certifications
35.1 lb	UL 508A
	CSA C22.2.
	NEMA

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

AC consolet

Cover type

Hinged

Mounting method

Surface

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Continuous hinge, plated screws

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - AC-16C30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)