

Eaton AC-20C20SS

Catalog Number: AC-20C20SS

Eaton B-Line series console enclosures, 20" height, 13.12" length, 20" width, NEMA 12, Screw cover, ACSS conolet, Surface mounted, Medium single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series console enclosures	AC-20C20SS
UPC	Product Length/Depth
782051146974	13.12 in
Product Height	Product Width
20 in	20 in
Product Weight	Certifications
31.7 lb	UL 508A
	CSA C22.2.
	NEMA

Material/finish

Material

304 stainless steel

Wall thickness

14 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Medium single door

Model

ACSS consolet

Cover type

Screw

Mounting method

Surface

Mounting hole details

External mounting feet

Closure type

Continous hinge

Special features

Stainless screws

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - AC-20C20SS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)