

Eaton AC-8C12SS

Catalog Number: AC-8C12SS

Eaton B-Line series consolelet enclosures, 8" height, 7.12" length, 12" width, NEMA 12, Screw cover, ACSS concolet, Surface mounted, Medium single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series consolelet enclosures	AC-8C12SS
UPC	Product Length/Depth
782051140767	7.12 in
Product Height	Product Width
8 in	12 in
Product Weight	Certifications
9.8 lb	UL 508A
	CSA C22.2.
	NEMA

Material/finish

Material

304 stainless steel

Wall thickness

14 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Medium single door

Model

ACSS consolet

Cover type

Screw

Mounting method

Surface

Mounting hole details

External mounting feet

Closure type

Continous hinge

Special features

Stainless screws

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - AC-8C12SS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)