

Eaton AC-8C20

Catalog Number: AC-8C20

Eaton B-Line series consolelet enclosures, 8" height, 7.12" length, 20" width, NEMA 12, Hinged cover, AC conolet, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series consolelet enclosures	AC-8C20
UPC	Product Length/Depth
782051410389	7.12 in
Product Height	Product Width
8 in	20 in
Product Weight	Certifications
14.5 lb	UL 508A
	CSA C22.2.
	NEMA

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

AC consolet

Cover type

Hinged

Mounting method

Surface

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Continous hinge, plated screws

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - AC-8C20](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)