

# Eaton B2055SS4

Catalog Number: B2055SS4

Eaton B-Line series O.D. pipe and conduit clamp, 0.1040" H x 6.4220" L x 1.25" W, Steel, 1000 Lbs load cap, 5/16"-18 bolt/pin size



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series O.D. pipe and conduit clamp	B2055SS4
	UPC
	781011870379
<b>Product Length/Depth</b>	<b>Product Height</b>
6.422 in	0.104 in
<b>Product Width</b>	<b>Product Weight</b>
1.25 in	0.62 lb
<b>Certifications</b>	
Not Applicable	

## Model

### Bolt/pin size

5/16"-18

### Special features

Include combination recess hex head machine screw

### Type

O.D pipe conduit clamp

## Load rating/capacity

### Load capacity

1000 lbs

## Material/finish

### Material

Steel

## Resources

### Catalogs

[Pipe clamps and hangers catalog section](#)

### Specifications and datasheets

[Eaton Specification Sheet - B2055SS4](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)