

Eaton DSC363212SS4

Catalog Number: DSC363212SS4

Eaton B-Line series wall mounted disconnect enclosure,36" height,12" length,32" width,NEMA 4X,Hinged cover,DSCSS4 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,304 stainless,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted disconnect enclosure	DSC363212SS4
	UPC
	799038654865
Product Length/Depth	Product Height
12 in	36 in
Product Width	Product Weight
32 in	90.6 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Product specifications

Special features

2-pt latching handle

Closure type

Hinged

Finish color

#4 brushed

Color

Gray

Wall thickness

14 gauge, 14 gauge

Material

304 stainless steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

Thru holes, optional external mounting feet

Locking provisions

Defeater padlock provision

NEMA Rating

4X

Model

DSCSS4 enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - DSC363212SS4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)