

# Eaton DSC363212SS6

Catalog Number: DSC363212SS6

Eaton B-Line series wall mounted disconnect enclosure,36" height,12" length,32" width,NEMA 4X,Hinged cover,DSCSS6 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,316 stainless,Seamless poured in-place gasket

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series wall mounted disconnect enclosure	DSC363212SS6
	<b>UPC</b>
	799038654872

<b>Product Length/Depth</b>	<b>Product Height</b>
12 in	36 in

<b>Product Width</b>	<b>Product Weight</b>
32 in	90.6 lb

### Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

2-pt latching handle

### Closure type

Hinged

### Finish color

#4 brushed

### Color

Gray

### Wall thickness

14 gauge, 14 gauge

### Material

316 stainless steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

### Locking provisions

Defeater padlock provision

### NEMA Rating

4X

### Model

DSCSS6 enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - DSC363212SS6](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)