

Eaton DSC423816SS6

Catalog Number: DSC423816SS6

Eaton B-Line series wall mounted disconnect enclosure,42" height,16" length,38" width,NEMA 4X,Hinged cover,DSCSS6 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,316 stainless,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted disconnect enclosure	DSC423816SS6
	UPC
	799038654957
Product Length/Depth	Product Height
16 in	42 in
Product Width	Product Weight
38 in	132.9 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

316 stainless steel

Wall thickness

14 gauge, 14 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Medium single door

Model

DSCSS6 enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

Thru holes, optional external mounting feet

Locking provisions

Defeater padlock provision

Closure type

Hinged

Special features

3-pt latching handle

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - DSC423816SS6](#)