

Eaton DSC483816

Catalog Number: DSC483816

Eaton B-Line series wall mounted disconnect enclosure,48" height,16" length,38" width,NEMA 4,Hinged cover,DSC enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted disconnect enclosure	DSC483816
	UPC
	782051411034
Product Length/Depth	Product Height
16 in	48 in
Product Width	Product Weight
38 in	183.7 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

14 gauge, 14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

DSC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

Thru holes, optional external mounting feet

Locking provisions

Defeater padlock provision

Closure type

Hinged

Special features

3-pt latching handle

Standards

NEMA Rating

4

Country of origin

US

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - DSC483816](#)