

# Eaton DSC483816SS6

Catalog Number: DSC483816SS6

Eaton B-Line series wall mounted disconnect enclosure,48" height,16" length,38" width,NEMA 4X,Hinged cover,DSCSS6 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,316 stainless,Seamless poured in-place gasket

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series wall mounted disconnect enclosure	DSC483816SS6
	<b>UPC</b>
	799038654971
<b>Product Length/Depth</b>	<b>Product Height</b>
16 in	48 in
<b>Product Width</b>	<b>Product Weight</b>
38 in	147.3 lb
<b>Certifications</b>	
UL 50	
CSA C22.2.	
NEMA	

## Material/finish

### Material

316 stainless steel

### Wall thickness

14 gauge, 14 gauge

### Finish color

#4 brushed

### Color

Gray

## Model

### Style

Medium single door

### Model

DSCSS6 enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

Thru holes, optional external mounting feet

### Locking provisions

Defeater padlock provision

### Closure type

Hinged

### Special features

3-pt latching handle

## Standards

### NEMA Rating

4X

### Country of origin

US

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - DSC483816SS6](#)