

Eaton DSC603816

Catalog Number: DSC603816

Eaton B-Line series wall mounted disconnect enclosure,60" height,16" length,38" width,NEMA 4,Hinged cover,DSC enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted disconnect enclosure	DSC603816

UPC
799038654858

Product Length/Depth
16 in

Product Height
60 in

Product Width
38 in

Product Weight
220.7 lb

Certifications

UL 50
CSA C22.2.
NEMA

Product specifications

Special features

3-pt latching handle

Closure type

Hinged

Finish color

Painted

Color

ANSI 61 gray

Wall thickness

14 gauge, 14 gauge

Material

Carbon steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

Thru holes, optional external mounting feet

Locking provisions

Defeater padlock provision

NEMA Rating

4

Model

DSC enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - DSC603816](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)