

Eaton DSC603816SS6

Catalog Number: DSC603816SS6

Eaton B-Line series wall mounted disconnect enclosure,60" height,16" length,38" width,NEMA 4X,Hinged cover,DSCSS6 enclosure,Wall mount,Large double door,Thru holes,opt. external mounting feet,316 stainless,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted disconnect enclosure	DSC603816SS6
	UPC
	799038655008
Product Length/Depth	Product Height
16 in	60 in
Product Width	Product Weight
38 in	176 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

316 stainless steel

Wall thickness

14 gauge, 14 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Large double door

Model

DSCSS6 enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

Thru holes, optional external mounting feet

Locking provisions

Defeater padlock provision

Closure type

Hinged

Special features

3-pt latching handle

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - DSC603816SS6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)