


Eaton SB5866090TG

Catalog Number: SB5866090TG

Eaton B-Line series open frame racks, Double sided, Steel, Telco gray powder coat, 12-24 panel mounting holes, Anchor plates, shims and anchors included, 48 mounting spaces, Top angle style, Seismic Zone 4, network bay open duct rack



General specifications

Product Name	Catalog Number
Eaton B-Line series open frame racks	SB5866090TG
UPC	Product Length/Depth
799038178835	90 in
Product Height	Product Width
90 in	23 in
Product Weight	Certifications
125.23 lb	UL Listed

Product specifications

Special features

48 mounting spaces

Type

Seismic Zone 4, network bay open duct rack

Style

Top angle

Material

Steel

Cover/door type

Double sided

Load capacity

340 lb

Material details

ASTM A570 grade 33 steel

Surface finish

Telco gray powder coat

Mounting rails

12-24 panel mounting holes

Resources

Brochures

[RCM and RCM+ brochure](#)

Specifications and datasheets

[Eaton Specification Sheet - SB5866090TG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)