

CP Non-Metallic, Armored Cable, and Flexible Metallic Conduit Fittings

- Armored Cable and Flexible Metallic Conduit Connectors
- Flexible Metallic Conduit Fittings

CP Cable Fittings

ARMORED CABLE AND FLEXIBLE METALLIC CONDUIT CONNECTORS – DIE CAST ZINC

Squeeze Type* - Straight - Insulated
UL File No. E-19188



Cat. #	Trade Size	Unit Qty	Std Pkg	Weight Lbs. Per 100
1707DC	3/8"	50	500	6
1708DC	1/2"	30	300	8
1709DC	3/4"	18	180	11
1710DC	1"	12	120	16
1711DC	1 1/4"	8	80	21
1712DC	1 1/2"	6	60	28
1713DC	2"	4	40	36
1714DC	2 1/2"	3	18	85
1715DC	3"	2	12	109
1721DC	3 1/2"	1	6	144
1722DC	4"	1	6	183

Squeeze Type* - Straight - Non-Insulated

Cat. #	Trade Size	Unit Qty	Std Pkg	Weight Lbs. Per 100
707DC	3/8"	50	500	6
708DC	1/2"	30	300	8
709DC	3/4"	18	180	11
710DC	1"	12	120	16
711DC	1 1/4"	8	80	21
712DC	1 1/2"	6	60	28
713DC	2"	4	40	36
714DC	2 1/2"	3	18	85
715DC	3"	2	12	109
721DC	3 1/2"	1	6	144
722DC	4"	1	6	183

ARMORED CABLE AND FLEXIBLE METALLIC CONDUIT CONNECTORS – MALLEABLE IRON

Features:

Male hub treads - NPSM

Standard Materials and Finishes

Malleable Iron • Finish: Zinc Plated
Steel locknut
Stamped steel covers

Clamp Type* 45° Angle – Non-Insulated

UL File No. E-19188
or E-19189



723



Cat. #	Trade Size	Diam. of Opening for Cable	Diam. of Bushed Hole	Unit Qty	Std Pkg	Wt Lbs./100
723	3/8"	2 1/32"	1 7/32"	50	200	14
		For 2 conductor No.'s 14, 12, 10 3 conductor No.'s 14, 12, 10 4 conductor No.'s 14, 12				
735	1/2"	1 5/16"	9/16"	25	100	18
		Flexible metallic conduit 5/16" and 3/8"				
		For 2 conductor No. 8				
737	3/4"	1 1/8"	2 5/32"	25	100	24
		Flexible metallic conduit 1/2"				
		For 2 conductor No.'s 6, 4 3 conductor No.'s 6, 4 Flexible metallic conduit 3/4"				

45° Angle – Insulated

UL File No. E-19188
or E-19189



1735



Cat. #	Trade Size	Diam. of Opening for Cable	Diam. of Bushed Hole	Unit Qty	Std Pkg	Wt Lbs./100
1723	3/8"	2 1/32"	1 7/32"	50	200	14
1735	1/2"	1 5/16"	9/16"	25	100	17
1737	3/4"	1 1/8"	2 5/32"	25	100	24