

CP Series 5 Combination Conduit Outlet Bodies For EMT and IMC or Rigid Conduit

- Combination Conduit Outlet Bodies
- Die Cast Aluminum
- Available in SnapPack™
- Stainless Steel Cover Screws

CP Outlet Bodies

EMT CONDUIT OUTLET BODIES – CAST ALUMINUM†

UL File No. E-15022

Applications

Die cast aluminium Series 5 Conduit Bodies are used in conduit systems to:

- Act as pull outlets for conductors being installed
- Provide openings for making splices and taps in conductors
- Act as mounting outlets for lighting fixtures and wiring devices
- Connect conduit sections
- Provide taps for branch conduit runs
- Make 90 degree bends in conduit runs
- Provide for access to conductors for maintenance and future system changes
- Conduit bodies are supplied with threaded hubs for use with IMC or Rigid conduit and set screws for use with EMT conduit

Type C



Cat. #	Trade Size	Internal Vol. in Cu. In.	Unit Qty	Std. Pkg	Wt Lbs. Per 100
C15-MT	1/2"	4.25	10	100	27
C25-MT	3/4"	7.0	10	50	40
C35-MT	1"	10.8	5	25	64
C45-MT	1 1/4"	32.3	2	10	165
C55-MT	1 1/2"	32.3	2	10	150
C65-MT	2"	64.0	1	5	270

† SnapPack™ EMT conduit bodies consisting of body and cover assembled and shipped together, change "-MT" to "-MTC" in catalog number i.e.: LB25-MTC

Type LL



Cat. #	Trade Size	Internal Vol. in Cu. In.	Unit Qty	Std. Pkg	Wt Lbs. Per 100
LL15-MT	1/2"	4.25	10	100	27
LL25-MT	3/4"	7.0	10	50	40
LL35-MT	1"	10.8	5	25	64
LL45-MT	1 1/4"	32.3	2	10	165
LL55-MT	1 1/2"	32.3	2	10	150
LL65-MT	2"	64.0	1	5	270

† SnapPack™ EMT conduit bodies consisting of body and cover assembled and shipped together, change "-MT" to "-MTC" in catalog number i.e.: LB25-MTC

Type LR



Cat. #	Trade Size	Internal Vol. in Cu. In.	Unit Qty	Std. Pkg	Wt Lbs. Per 100
LR15-MT	1/2"	4.25	10	100	27
LR25-MT	3/4"	7.0	10	50	40
LR35-MT	1"	10.8	5	25	64
LR45-MT	1 1/4"	32.3	2	10	165
LR55-MT	1 1/2"	32.3	2	10	150
LR65-MT	2"	64.0	1	5	270

† SnapPack™ EMT conduit bodies consisting of body and cover assembled and shipped together, change "-MT" to "-MTC" in catalog number i.e.: LB25-MTC


Type T



Cat. #	Trade Size	Internal Vol. in Cu. In.	Unit Qty	Std. Pkg	Wt Lbs. Per 100
T15-MT	1/2"	4.25	10	100	27
T25-MT	3/4"	7.0	10	50	40
T35-MT	1"	10.8	5	25	64
T45-MT	1 1/4"	32.3	2	10	165
T55-MT	1 1/2"	32.3	2	10	150
T65-MT	2"	64.0	1	5	270

† SnapPack™ EMT conduit bodies consisting of body, cover and gasket assembled and shipped together, change "-MT" to "-MTC" in catalog number i.e.: LB25-MTC

Type LB



Cat. #	Trade Size	Internal Vol. in Cu. In.	Unit Qty	Std. Pkg	Wt Lbs. Per 100
LB15-MT	1/2"	4.25	10	100	27
LB25-MT	3/4"	7.2	10	50	40
LB35-MT	1"	10.8	5	25	64
LB45-MT	1 1/4"	28.8	2	10	132
LB55-MT	1 1/2"	32.3	2	10	175
LB65-MT	2"	66.5	1	5	240
LB75-MT*	2 1/2"	Over 100	1	1	450
LB85-MT*	3"	Over 100	1	1	460
LB95-MT*	3 1/2"	Over 100	1	1	800
LB105-MT*	4"	Over 100	1	1	900

† SnapPack™ EMT conduit bodies consisting of body, cover and gasket assembled and shipped together, change "-MT" to "-MTC" in catalog number i.e.: LB25-MTC

* Fittings greater than 2" are set-screw only (not combination threaded & set-screw)

Covers, Aluminum



Cat. #	Conduit Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
150	1/2"	50	250	5
250	3/4"	50	250	6
350	1"	50	250	20
450	1 1/4"-1 1/2"	50	50	25
650	2"	25	25	25
850D	2 1/2"-3"	10	10	78
950D	3 1/2"-4"	5	5	140

Gaskets, Neoprene



Cat. #	Conduit Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
GASK015N	1/2"	100	100	2
GASK025N	3/4"	100	100	2
GASK035N	1"	50	50	3
GASK045N	1 1/4"-1 1/2"	50	50	6
GASK065N	2"	25	25	10
GASK085N	2 1/2"-3"	10	10	20
GASK095N	3 1/2"-4"	10	10	30

Series 5 Conduit Outlet Bodies For Rigid/IMC Conduit

- Rigid Conduit Outlet Bodies
- Die Cast Aluminum
- Available in SnapPack™†

CP

CP Outlet Bodies

RIGID CONDUIT OUTLET BODIES – CAST ALUMINUM

Type C †



Cat. #	Trade Size	Internal Volume in Cubic Inches	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
C15	1/2"	4.25	10	100	27
C25	3/4"	7.0	10	50	40
C35	1"	10.8	5	25	64
C45	1 1/4"	32.3	2	10	165
C55	1 1/2"	32.3	2	10	150
C65	2"	64.0	1	5	270
C75	2 1/2"	Over 100	1	1	500
C85	3"	Over 100	1	1	600
C95*	3 1/2"	Over 100	1	1	900
C105*	4"	Over 100	1	1	1000

*Not UL Listed

Type LL †



Cat. #	Trade Size	Internal Volume in Cubic Inches	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
LL15	1/2"	4.25	10	100	30
LL25	3/4"	7.0	10	50	48
LL35	1"	10.8	5	25	64
LL45	1 1/4"	32.3	2	10	140
LL55	1 1/2"	32.3	2	10	160
LL65	2"	63.0	1	5	270
LL75	2 1/2"	Over 100	1	1	500
LL85	3"	Over 100	1	1	600
LL95	3 1/2"	Over 100	1	1	900
LL105	4"	Over 100	1	1	1000

Type LR †



Cat. #	Trade Size	Internal Volume in Cubic Inches	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
LR15	1/2"	4.25	10	100	26
LR25	3/4"	7.0	10	50	48
LR35	1"	10.8	5	25	64
LR45	1 1/4"	32.3	2	10	140
LR55	1 1/2"	32.3	2	10	160
LR65	2"	63.0	1	5	260
LR75	2 1/2"	Over 100	1	1	500
LR85	3"	Over 100	1	1	600
LR95	3 1/2"	Over 100	1	1	900
LR105	4"	Over 100	1	1	1000

Type T †



Cat. #	Trade Size	Internal Volume in Cubic Inches	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
T15	1/2"	4.25	10	100	32
T25	3/4"	7.0	10	50	46
T35	1"	10.8	5	25	70
T45	1 1/4"	32.3	2	10	175
T55	1 1/2"	32.3	2	10	185
T65	2"	64.0	1	2	300
T75	2 1/2"	Over 100	1	1	550
T85	3"	Over 100	1	1	650
T95*	3 1/2"	Over 100	1	1	950
T105*	4"	Over 100	1	1	1050

*Not UL Listed

Type LB †



Cat. #	Trade Size	Internal Volume in Cubic Inches	Unit Qty.	Std. Pkg.	Weight Lbs. Per 100
LB15	1/2"	4.25	10	100	27
LB25	3/4"	7.2	10	50	40
LB35	1"	10.8	5	25	56
LB45	1 1/4"	28.8	2	10	132
LB55	1 1/2"	32.3	2	10	175
LB65	2"	66.5	1	5	240
LB75	2 1/2"	Over 100	1	1	450
LB85	3"	Over 100	1	1	460
LB95	3 1/2"	Over 100	1	1	800
LB105	4"	Over 100	1	1	900

Covers, Aluminum



Cat. #	Conduit Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
150	1/2"	50	250	5
250	3/4"	50	250	6
350	1"	50	250	20
450	1 1/4"-1 1/2"	50	50	25
650	2"	25	25	25
850D	2 1/2"-3"	10	10	78
950D	3 1/2"-4"	5	5	140

Gaskets, Neoprene



Cat. #	Conduit Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
GASK015N	1/2"	100	100	2
GASK025N	3/4"	100	100	2
GASK035N	1"	50	50	3
GASK045N	1 1/4"-1 1/2"	50	50	6
GASK065N	2"	25	25	10
GASK085N	2 1/2"-3"	10	10	20
GASK095N	3 1/2"-4"	10	10	30

Options:

†SnapPack™ pre-packaged body, cover and neoprene gasket add suffix CGN ie. LB25-CGN