

# Conduit Outlet Bodies Series 5 Dimensions

- Rigid and combination Rigid or IMC and EMT Conduit Outlet Bodies
- Die Cast Aluminum

### Type LB Dimensions – Threaded & Set Screw Conduit

Size	A	B	C	D	E	F
1/2"	1 1/32"	1 57/64"	1/2"	2 11/64"	4 13/32"	1 5/32"
3/4"	1 35/64"	4 49/64"	3/4"	2 7/16"	5 1/8"	1 3/8"
1"	1 3/4"	5 3/8"	1"	2 3/4"	5 15/16"	1 23/32"
1 1/4"	2 35/64"	7 15/64"	1 1/4"	3 35/64"	7 7/8"	2 15/64"
1 1/2"	2 19/32"	7 17/64"	1 1/2"	3 23/32"	7 7/8"	2 3/8"
2"	3 13/64"	9 33/64"	2"	4 1/4"	10 15/64"	2 29/32"
2 1/2"	4 1/2"	12 3/16"	2 1/2"	5 5/32"	12 3/4"	3 13/32"
3"	4 15/32"	12 17/64"	3"	5 21/32"	12 43/64"	4 1/64"
3 1/2"	5 39/64"	15 1/32"	3 1/2"	6 61/64"	15 35/64"	5 5/32"
4"	5 39/64"	15 1/32"	4"	6 61/64"	15 35/64"	5 5/32"

### Type C Dimensions – Threaded & Set Screw Conduit

Size	A	B	C	D	E	F
1/2"	1 5/16"	3 27/32"	1/2"	1 1/2"	4 27/32"	1 1/8"
3/4"	1 17/32"	4 19/32"	3/4"	1 5/8"	5 41/64"	1 1/16"
1"	1 3/4"	5 11/32"	1"	1 29/32"	6 1/2"	1 1/2"
1 1/4"	2 17/32"	7 1/4"	1 1/4"	2 3/4"	8 1/2"	2 1/4"
1 1/2"	2 17/32"	7 1/4"	1 1/2"	2 3/4"	8 1/2"	2 1/4"
2"	2 7/32"	9 7/16"	2"	3 13/32"	10 3/4"	2 3/4"
2 1/2"	4 1/2"	12 1/4"	2 1/2"	4 1/2"	13"	4 1/2"
3"	4 1/2"	12 1/4"	3"	4 1/2"	13"	4 1/2"
3 1/2"	5 1/2"	15"	3 1/2"	5 9/16"	16 5/16"	5 1/2"
4"	5 1/2"	15"	4"	5 9/16"	16 5/16"	5 1/2"

### Type LL Dimensions – Threaded & Set Screw Conduit

Size	A	B	C	D	E	F
1/2"	1 3/32"	3 7/8"	1/2"	2"	4 9/32"	1 13/32"
3/4"	1 1/4"	4 21/32"	3/4"	2 11/32"	5 1/8"	1 13/32"
1"	1 1/2"	5 23/64"	1"	2 1/2"	5 99/64"	1 7/8"
1 1/4"	2 1/4"	7 17/64"	1 1/4"	3 13/32"	7 55/64"	2 7/8"
1 1/2"	2 1/4"	7 17/64"	1 1/2"	3 13/32"	7 55/64"	2 7/8"
2"	2 3/4"	9 15/32"	2"	3 27/32"	10 13/64"	3 27/64"
2 1/2"	4 5/8"	12 1/4"	2 1/2"	5 3/4"	13"	4 1/2"
3"	4 5/8"	12 1/4"	3"	5 3/4"	13"	4 1/2"
3 1/2"	5 7/16"	15"	3 1/2"	6 1/8"	16 5/16"	5 9/16"
4"	5 7/16"	15"	4"	6 1/8"	16 5/16"	5 9/16"

### Type LR Dimensions – Threaded & Set Screw Conduit

Size	A	B	C	D	E	F
1/2"	1 7/64"	3 7/8"	1/2"	2"	4 9/32"	1 13/32"
3/4"	1 1/4"	4 21/32"	3/4"	2 11/32"	5 1/8"	1 141/64"
1"	1 1/2"	5 23/64"	1"	2 1/2"	5 59/64"	1 7/8"
1 1/4"	2 1/4"	7 17/64"	1 1/4"	3 13/32"	7 55/64"	2 7/8"
1 1/2"	2 1/4"	7 17/64"	1 1/2"	3 13/32"	7 55/64"	2 7/8"
2"	2 3/4"	9 15/32"	2"	3 27/32"	10 13/64"	3 27/64"
2 1/2"	4 7/16"	12 1/4"	2 1/2"	5 3/16"	12 1/4"	4 1/2"
3"	4 5/8"	12 1/4"	3"	5 3/16"	12 1/4"	4 1/2"
3 1/2"	5 7/16"	15"	3 1/2"	6 1/8"	15"	6 1/4"
4"	5 7/16"	15"	4"	6 1/8"	15"	6 1/4"

### Type T Dimensions – Threaded & Set Screw Conduit

Size	A	B	C	D	E	F
1/2"	1 5/16"	3 27/32"	1/2"	1 3/8"	4 27/32"	2 1/16"
3/4"	1 17/16"	4 39/64"	3/4"	1 41/64"	5 19/32"	2 11/32"
1"	1 25/32"	5 3/8"	1"	1 29/32"	6 1/2"	2 19/32"
1 1/4"	2 1/2"	7 1/4"	1 1/4"	2 3/4"	8 1/2"	3 35/64"
1 1/2"	2 1/2"	7 1/4"	1 1/2"	2 3/4"	8 1/2"	3 35/64"
2"	3 1/4"	9 7/16"	2"	3 27/64"	10 13/16"	4 3/64"
2 1/2"	4 1/2"	12 1/4"	2 1/2"	4 1/2"	13"	5 25/32"
3"	4 1/2"	12 1/4"	3"	4 1/2"	13"	5 25/32"
3 1/2"	5 1/2"	15"	3 1/2"	5 9/16"	16 5/16"	6 13/16"
4"	5 1/2"	15"	4"	5 9/16"	16 5/16"	6 13/16"

