

37499

ELECTRIC CLNR & LUBRICATING SP

UPC: 08593737499

Country of Origin:

UNSPSC: 47131821

USA

Commodity: Degreasing compounds



Sprayon® Electrical Cleaner & Lubricating Spray, 16 oz

Product Attributes

Brand Name	Cully
Sub Brand	Sprayon®
Type	Electronic Contact Cleaner and Protectant
Special Features	Penetrating, Fast Evaporation, Can be used while current exist, Protects Against Corrosion, Dielectric Strength 36.7KV, KB Solvency Strength: 129, Safe for Most Plastic
Application	Cleans and Lubricates on the following: Switches, relays, timers, signals, transmitters, condensers, transistors, microphones, panel Boards, circuit Breakers, contacts, meters, receivers, speakers, coils
Standard	NSF® Registered K2 #115081
Size	16FL oz
Container	16oz Aluminum Aerosol Can
Form	Liquid
Color	Clear
Composition	Trichloroethylene (79-01-6), Carbon Dioxide (124-38-9)
Storage Temperature	Do not store above 120°F
Flammability	Non Flammable, HMIS Rating: 0
Density	Heavier than air
Specific Gravity	1.45
Shelf Life	3 years from date of manufacture
Fragrance	Strong

Compliance Information

Buy America Act Compliant:	Unspecified
Buy American Act Compliant:	Unspecified
RoHS Compliant:	Unspecified
UL Compliant:	No
UL Code:	N/A

Proposition 65



WARNING: This product can expose you to chemicals, which is known to the State of California to cause cancer and reproductive harm. For more information go to www.P65Warnings.ca.gov.

Item Status: Active

Standard Qty: 1

Minerallac Company

Tel: 800-927-3293

Fax: 800-824-8942

www.minerallac.com

WARRANTY DISCLAIMER The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

Remedy/Liability Limits The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .