

39820-6

#10 PH COMBO ANCHOR JAR 200

UPC: 08593707366

Country of Origin:

UNSPSC: 31162103

USA

Commodity: Wall anchors



*#10 Phillips/Slotted Pan Head Red Conical Anchor Kit,
#10 x 1" (200), #10-12 (200), Includes 1/4" Carbide Drill
Bit*

Product Attributes

Brand Name	Minerallac
Sub Brand	Cully
Type	Plastic Anchor
Application	The conical plastic anchor is a light-duty part that can be used in drywall, concrete, and hollow block or brick.
Size	#10 – #12
Length	1.000" IN
Minimum Embedment	1.000" IN
Depth	
Drill Size	1/4" IN
Screw Size	#10 x 1.000" IN
Material	Engineered Plastic
Tension Strength	In 4,000 PSI Concrete: 550 LB; in hollow brick: 350 LB; in solid red brick: 280 LB
Shear Strength	In 4,000 PSI Concrete: 350 LB; in hollow brick: 280 LB; in solid red brick: 320 LB
Kit Includes	401 piece kit consisting of: 200 pc(s) #10 x 1" slotted / phillips combo pan head fasteners; 200 pc(s) #10 – #12 anchors; 1 pc(s) 1/4" carbide bit

Compliance Information

Buy America Act Compliant:	Unspecified
Buy American Act Compliant:	Unspecified
RoHS Compliant:	Unspecified
UL Compliant:	No
UL Code:	N/A

Proposition 65

This product is in compliance with Prop65; it is not known to contain any chemicals associated with this regulation.

Item Status: Active

Standard Qty: 1

Minerallac Company

Tel: 800-927-3293
Fax: 800-824-8942
www.minerallac.com

WARRANTY DISCLAIMER The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

Remedy/Liability Limits The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .