

**55208J**

**5/16-18 X 1/2 HEX TAP BOLT ZP**

UPC: 08593701911

Country of Origin:

UNSPSC: 31161501

TAIWAN

Commodity: Cap screws



*5/16-18 x 1/2" Tap Bolts, Hex Head, Full Thread, Grade 2, Zinc, Jar*

**Product Attributes**

|                  |  |
|------------------|--|
| Brand Name       | Minerallac   |
| Sub Brand        | Cully  |
| Type             | Hex Cap Bolt                                       |
| Special Features | Made of medium carbon steel—quenched and tempered. |
| Material         | Grade 2 Steel                                      |
| Size             | 5/16-18 x 1/2" IN                                  |
| Length           | 1/2" IN  |
| Thread Type      | Coarse   |
| Thread Size      | 18 TPI   |
| Head Width       | 1/2" IN  |
| Head Height      | 13/64" IN  |
| Head Type        | Hex Head   |
| Head Color       | Silver   |
| Finish           | Zinc Plated  |

**Compliance Information**

|                             |             |
|-----------------------------|-------------|
| Buy America Act Compliant:  | Unspecified |
| Buy American Act Compliant: | Unspecified |
| RoHS Compliant:             | Unspecified |
| UL Compliant:               | No          |
| UL Code:                    | N/A         |

**Proposition 65**

This product is in compliance with Prop65; it is not known to contain any chemicals associated with this regulation.

Item Status: Active

Standard Qty: 100

**Minerallac Company**

Tel: 800-927-3293  
Fax: 800-824-8942  
www.minerallac.com

**WARRANTY DISCLAIMER** The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

**Remedy/Liability Limits** The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .