

55442BFG

3/8-16 X 2-1/2 HEX TAP BOLT ZP


UPC: 08593702849

Country of Origin:

UNSPSC: 31161620

CHINA

Commodity: Hexagonal bolts



3/8-16 x 2-1/2" Tap Bolts, Hex Head, Full Thread, Grade 2, Zinc, Jar

Product Attributes

Brand Name	Minerallac
Sub Brand	Cully
Type	Hex Tap Bolt
Application	To be used in drilled and tapped holes which are threaded full length.
Material	Steel
Finish	Zinc Plated
Head Type	Hex
Length	2.500" IN
Size	3/8"-16 x 2-1/2" IN
Diameter	0.375" IN
Thread	16 TPI

Compliance Information

Buy America Act Compliant:	No
Buy American Act Compliant:	No
RoHS Compliant:	No
UL Compliant:	No
UL Code:	N/A

Proposition 65

This product is in compliance with Prop65; it is not known to contain any chemicals associated with this regulation.

Item Status: Active

Standard Qty: 500

Minerallac Company

Tel: 800-927-3293
Fax: 800-824-8942
www.minerallac.com

WARRANTY DISCLAIMER The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

Remedy/Liability Limits The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .