

59011J	3/16 x 7/8 ZAMAC NAILIN
---------------	--------------------------------

UPC: 08593704344 Country of Origin: VIETNAM
 UNSPSC: 31162107
 Commodity: Nail expansion anchors



3/16 x 7/8" Zamac Hammer Drive Nailin Anchors, Light Duty Concrete, Solid Brick or Block, Jar

Product Attributes	
Brand Name	Minerallac
Sub Brand	Cully
Type	Hammer Drive Anchors
Special Features	Features include ease of installation, immediate loading capabilities, and the tamper-resistant nature of the finished assembly.
Application	They are designed for attaching termination bar to solid concrete, solid brick, block or masonry walls.
Size	3/16" x 7/8" IN
Diameter	0.188" IN
Length	0.750" IN
Minimum Embedment Depth	0.625" IN
Drill Size	3/16" IN
Head Diameter	0.406" IN
Head Type	Mushroom Head
Material	Zinc Alloy
Finish	Zinc Plated
Warning	Not recommended for vibrating loads or overhead installations

Compliance Information	
Buy America Act Compliant:	Unspecified
Buy American Act Compliant:	Unspecified
RoHS Compliant:	Unspecified
UL Compliant:	No
UL Code:	N/A

Proposition 65	
This product is in compliance with Prop65; it is not known to contain any chemicals associated with this regulation.	

Item Status:	Active
Standard Qty:	100

Minerallac Company	
Tel: 800-927-3293	
Fax: 800-824-8942	
www.minerallac.com	

WARRANTY DISCLAIMER The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

Remedy/Liability Limits The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .