

<b>61822J</b>	<b>1/2 x 2-1/4 HEX SLEEVE ANC ZP</b>
---------------	--------------------------------------

UPC: 08593704346 Country of Origin: CHINA  
 UNSPSC: 31162101  
 Commodity: Concrete anchors



*1/2 x 2-1/4" Sleeve Anchors, Medium Duty, Hex, Used in Cinder Block, Brick, Thin Wall and Concrete, Zinc Plated, Jar*

Product Attributes	
Brand Name	Minerallac
Sub Brand	Cully
Type	Concrete Anchor
Special Features	Can be removed after it's been installed. Length of the sleeve induces less stress on the substrate than does a wedge anchor/
Application	Well-suited for permanently anchoring heavy equipment to concrete.
Size	1/2 x 2-1/4" IN
Diameter	0.500" IN
Length	2.250" IN
Minimum Embedment Depth	1.625" IN
Drill Size	3/8" IN
Head Diameter	0.500" IN
Head Type	Hex Nut
Material	Steel
Finish	Zinc Plated
Tension Strength	2700 PSI
Shear Strength	3250 PSI

Compliance Information	
Buy America Act Compliant:	Unspecified
Buy American Act Compliant:	Unspecified
RoHS Compliant:	Unspecified
UL Compliant:	No
UL Code:	N/A

Proposition 65	
This product is in compliance with Prop65; it is not known to contain any chemicals associated with this regulation.	

Item Status:	Active
Standard Qty:	25

Minerallac Company	
Tel: 800-927-3293	
Fax: 800-824-8942	
www.minerallac.com	

**WARRANTY DISCLAIMER** The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

**Remedy/Liability Limits** The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product. IN NO CASE SHALL MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .