

**62898US**

**3/4 X 7 STUD WEDGE ANCHOR**

UPC: 08593701129

Country of Origin:

UNSPSC: 31162102

**USA**

Commodity: Wedge anchors



*3/4 X 7, Wedge anchors, also known as expansion bolts and expansion anchors, are four-piece anchor assemblies that secure themselves using a*

**Product Attributes**

Brand Name	Minerallac
Sub Brand	Cully
Type	Wedge Anchor
Special Features	Designed for full-contact expansion.
Application	These are heavy-duty, non-bottom bearing anchors of greater shear strength than other light and medium-duty expansion anchors for use in concrete and stone.
Diameter	3/4" IN
Length	7" IN
Minimum Embedment Depth	3-1/4" IN
Thread Type	Coarse
Thread Size	3/4" IN
Thread Length	2-1/4" IN
Thread per Inch	10 TPI
Drill Size	3/4" IN
Material	Steel
Finish	Zinc Plated
ICC EVALUATION SVC	No ICC listing

**Compliance Information**

Buy America Act Compliant:	No
Buy American Act Compliant:	Yes
RoHS Compliant:	Unspecified
UL Compliant:	No
UL Code:	N/A

**Proposition 65**

This product is in compliance with Prop65; it is not known to contain any chemicals associated with this regulation.

Item Status: Active

Standard Qty: 10

**Minerallac Company**

Tel: 800-927-3293  
Fax: 800-824-8942  
www.minerallac.com

**WARRANTY DISCLAIMER** The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

**Remedy/Liability Limits** The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner .