

82308

1/2 X 18 BELLHANGER DRILL

UPC: 085937823083


Country of Origin:

UNSPSC: 23241634

Taiwan

Commodity: Jobber length drill

The Carbide Tipped Bell Hanger is designed for making holes and fishing wire through these holes for all electrical, telephone, security-alarm, structured wiring systems or any small wire installation.



Product Attributes

Brand Name	Minerallac Company
Sub Brand	Cully
Type	Bellhanger Bit
Special Features	Hole in head of bit for easy pulling of wire.
Application	To drill into wood
Material	Middle Carbon Steel
Finish	Polished
Point Type	Non-screw Tip
Drill Point	82°
Fractional Size	1/2" IN
Flute Length	4-3/4" IN
Overall Length	18" IN
Shank Diameter	1/2" IN
Shank Type	Round Shank
Number of Pieces	1

Item Status: Active

Standard Qty: 1

Minerallac Company

Tel: 800-927-3293

Fax: 800-824-8942

www.minerallac.com