

82408

1/2 X 24 BELLHANGER DRILL


UPC: 085937824080

Country of Origin:

UNSPSC: 23241634

**Taiwan**

Commodity: Jobber length drill



*The Carbide Tipped Bell Hanger is designed for making holes and fishing wire through these holes for all electrical, telephone, security-alarm, structured wiring systems or any small wire installation.*

**Product Attributes**

Brand Name	Minerallac Company
Sub Brand	Cully
Type	Bellhanger Bit
Special Features	Hole in head of bit for easy pulling of wire.
Application	To drill into wood
Material	Middle Carbon Steel
Finish	Polished
Point Type	Non-screw Tip
Drill Point	82°
Fractional Size	1/2" IN
Flute Length	4.72" IN
Overall Length	24" IN
Shank Diameter	1/2" IN
Shank Type	Round Shank
Number of Pieces	1

Item Status: Active

Standard Qty: 1

Minerallac Company

Tel: 800-927-3293

Fax: 800-824-8942

www.minerallac.com