

92057

3/4 X 72 FLEX SHANK FISHBIT

UPC: 085937920577

Country of Origin:

UNSPSC: 27111537

Taiwan

Commodity: Wood auger bit



Unique flexible self feeding bits for drilling holes down the length of wall cavities and through hidden studs with no damage to wall board, plaster, or any exterior finish.

Product Attributes

Brand Name	Minerallac Company
Sub Brand	Cully
Type	Flexible Installer Bit
Special Features	Features a long flexible shank and self-feeding screw point.
Application	For any application where drilling behind a wall of other hard to reach locations.
Standard	N/A
Bit Diameter	3/4" IN
Overall Length	72" IN
Shank Diameter	1/4" IN
Twist Length	N/A
Number Of Flutes	1
Flute Type	Parabolic Flute
Shank Type	Flex Shank
Material	Spring Steel
Finish	Polished

Item Status: Active

Standard Qty: 1

Minerallac Company

Tel: 800-927-3293

Fax: 800-824-8942

www.minerallac.com