

92629

29/64 TRINADO DRILL W 3/8 SHAN

UPC: 085937926296

Country of Origin:

UNSPSC: 23241634

USA

Commodity: Jobber length drill



These heavy-duty Trinado Drills are jobber-length drill bits, made from high-speed steel, that have a polished flute for easy chip removal.

Product Attributes

Brand Name	Minerallac Company
Sub Brand	Cully
Type	HSS Jobber Length Drill
Special Features	Heavy-Duty Construction
Material	High Speed Steel
Finish	Black Oxide
Point Type	135°
Drill Point	Split Point
Fractional Size	29/64" IN
Flute Length	4-3/16" IN
Overall Length	5-5/8" IN
Shank Diameter	3/8" IN
Number of Pieces	1

Item Status: Active
Standard Qty: 6

Minerallac Company

Tel: 800-927-3293
Fax: 800-824-8942
www.minerallac.com