

Eaton 10250T pushbutton

10250H2738

UPC:782113223056

Dimensions:

- **Height:** 5 IN
- **Length:** 3.6 IN
- **Width:** 3.4 IN

Weight: .5 LB

Notes: Open type enclosure. Round button.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Flush
- **Enclosure:** NEMA 3, 3R, 4, 4X, 13
- **Enclosure Material:** Die cast
- **Illumination:** PresTest
- **Legend:** START
- **Mounting:** Horizontal, vertical
- **Nema Rating:** NEMA 3, 3R, 4, 12, 13
- **Number Of Elements:** 1
- **Product Category:** Assembled control station
- **Series:** 10250H

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250H2738](#)

Certifications:

- CSA Certified
- UL 505

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.