

Specifications



Photo is representative



Eaton 1244C52G12

Eaton Navy and Marine complete molded case circuit breaker, AQB-A50, Complete breaker, Non-interchangeable thermal-magnetic trip type, 25A trip rating, Three-pole, 500 V, 5 kAIC, Naval, 400 Hz

General specifications

PRODUCT NAME	Eaton Navy & Marine complete molded case circuit breaker
CATALOG NUMBER	1244C52G12
UPC	786679849330
PRODUCT LENGTH/DEPTH	4.8 in
PRODUCT HEIGHT	3.7 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	2.6 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	MIL-DTL-17361



Powering Business Worldwide

Product specifications

VOLTAGE RATING	500 Vac
TRIP TYPE	Non-interchangeable thermal-magnetic
CIRCUIT BREAKER TYPE	AQB-A50
CIRCUIT BREAKER FRAME TYPE	Complete breaker
FREQUENCY RATING	400 to 415 Hz
CLASS	Naval
INTERRUPT RATING	5 kAIC
NUMBER OF POLES	Three-pole
TRIP RATING	25 A

Resources

CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1244C52G12

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

