

# Specifications



Photo is representative



Powering Business Worldwide

# Eaton 2606D58G19

Eaton molded case circuit breakers electrical aftermarket accessory shunt trip, Field mounting shunt trip, G19, 120 V, NB, HNB Breakers, Frame J-K

## General specifications

<b>PRODUCT NAME</b>	Eaton molded case circuit breakers electrical aftermarket accessory shunt trip
<b>CATALOG NUMBER</b>	2606D58G19
<b>UPC</b>	786679936054
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	Contact Manufacturer
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	120V suitable for 55% pickup for ground fault applications. Not field mountable on non-automatic breakers/molded case switches. Field mounting voids UL listing except on LA,HLA,MA,HMA,NB,HNB,PB,KB,HKB,KA,HKA,LB,HLB and SELTRONIC breakers.

## Product specifications

<b>USED WITH</b>	NB, HNB breakers
<b>TYPE</b>	Field mounting shunt trip
<b>SPECIAL FEATURES</b>	G19
<b>VOLTAGE RATING</b>	120 V
<b>FRAME SIZE</b>	Frame J-K
<b>MOUNTING METHOD</b>	Right

## Resources

<b>CATALOGS</b>	<a href="#">Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2</a>
<b>MULTIMEDIA</b>	<a href="#">Flex shaft handle installation tutorial</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - 2606D58G19</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.