

Specifications

Eaton 2609D60G29



Photo is representative

Eaton Navy and Marine complete molded case circuit breaker, HMAM, Fixed thermal, fixed magnetic trip type, 2000-4000A trip rating, Three-pole, 800A, 1000 V, 18 kAIC at 1000 V, 120 V

General specifications

PRODUCT NAME	Eaton Navy & Marine complete molded case circuit breaker
CATALOG NUMBER	2609D60G29
UPC	786679517383
PRODUCT LENGTH/DEPTH	1.1 in
PRODUCT HEIGHT	1.1 in
PRODUCT WIDTH	1.1 in
PRODUCT WEIGHT	1.1 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

AMPERAGE RATING	800 A
VOLTAGE RATING	1000 V AC
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	HMAM
MAGNETIC TRIP RANGE	2000-4000A
UNDERVOLTAGE RELEASE	120 Vac
INTERRUPT RATING	18 kAIC at 1000 Vac
NUMBER OF POLES	Three-pole

Resources

BROCHURES	Breaker service centers
CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2 Aftermarket, Renewal Parts and Life Extension Solutions, Molded-Case Circuit Breakers, Volume 12, Tab 3
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 2609D60G29

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.