

# Specifications



## Eaton BABF1020

Eaton BAB thermal magnetic circuit breaker, Classic replacement circuit breaker, 15 A, 10 kAIC at 120/240 V, Single-pole, 120/240 V, #14-8 AWG Cu/Al, BQL

### General specifications

<b>PRODUCT NAME</b>	Eaton BAB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	BABF1020
<b>UPC</b>	786685405063
<b>PRODUCT LENGTH/DEPTH</b>	3.25 in
<b>PRODUCT HEIGHT</b>	3.5 in
<b>PRODUCT WIDTH</b>	0.875 in
<b>PRODUCT WEIGHT</b>	0.2 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	NFPA 72 HACR Rated
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	BAB
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Bolt-on Fire Alarm Circuit Breaker
<b>WIRE SIZE</b>	#14-8 AWG Cu/Al

## Resources

<b>MULTIMEDIA</b>	<a href="#">Circuit Breakers Explained</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BABF1020</a>

## Performance Ratings

<b>AMPERAGE RATING</b>	20 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>VOLTAGE RATING</b>	120/240 V

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.