

Specifications



Eaton BQ225225

Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Two-Pole 25 A, 10 kAIC, Four-pole, 120/240V, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ, Type BR Loadcenters

General specifications

PRODUCT NAME	Eaton BR thermal magnetic circuit breaker
CATALOG NUMBER	BQ225225
UPC	786676370950
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.75 lb
COMPLIANCES	Federal Specifications Classification W-C375
CERTIFICATIONS	UL 489
CATALOG NOTES	All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.



Powering Business Worldwide

Product specifications

USED WITH	Type BR Loadcenters
TYPE	Type BQ 1-Inch CTL plug-on circuit breaker
SPECIAL FEATURES	Includes rejection tab feature
AMPERAGE RATING	(2) Two-Pole 25A
VOLTAGE RATING	120/240 V
TRIP TYPE	T194
CIRCUIT BREAKER TYPE	BQ
MOUNTING METHOD	Plug-on
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	BQ
WIRE SIZE	#14-4 AWG Cu/Al
NUMBER OF POLES	Four-pole
QUANTITY	28

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BQ225225
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.