

# Specifications



Photo is representative

## Eaton CHF120CS

Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker clamshell pack, Clamshell pack, 20 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHF

### General specifications

<b>PRODUCT NAME</b>	Eaton CH thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	CHF120CS
<b>UPC</b>	786685683225
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	6.5 in
<b>PRODUCT WIDTH</b>	4.5 in
<b>PRODUCT WEIGHT</b>	0.4 lb
<b>WARRANTY</b>	Limited lifetime
<b>COMPLIANCES</b>	HACR Rated
<b>CERTIFICATIONS</b>	UL Listed CSA Certified



Powering Business Worldwide

## Product specifications

<b>USED WITH</b>	Type CH Loadcenters
<b>TYPE</b>	Type CHF 3/4-Inch standard circuit breaker clamshell pack
<b>SPECIAL FEATURES</b>	Clamshell pack
<b>AMPERAGE RATING</b>	20 A
<b>VOLTAGE RATING</b>	120/240 V
<b>TRIP TYPE</b>	Trip flag
<b>CIRCUIT BREAKER TYPE</b>	CHF
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHF
<b>WIRE SIZE</b>	(2) #14-10 AWG Cu/Al (1) #14-8 AWG
<b>NUMBER OF POLES</b>	Single-pole

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHF120CS</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.