

A200 Heater

FH77

UPC:786678670751

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Used with A200 Starter Sizes 3 &4, 3-Phase Only
- **Type:** A200 Heater
- **Design:** NEMA
- **Full Load Current Range:** Ambient 30.7-33.5A, Non-Comp 28.2-30.8A
- **Overload Relay:** Type A and B
- **Trip Type:** Thermal and Fast Trip

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)
- [Eaton Specification Sheet - FH77](#)

Certifications:

- CSA Certified
- UL Listed

