

Specifications



Photo is representative



Eaton GHQ1030

Eaton GHQ thermal magnetic circuit breaker, 30 A, 14 kAIC, Single-pole, 277/480, GHP

General specifications

PRODUCT NAME	Eaton GHQ thermal magnetic circuit breaker
CATALOG NUMBER	GHQ1030
UPC	786689030506
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	0.6 in
PRODUCT WEIGHT	0.49 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	GHP
NUMBER OF POLES	Single-pole
TYPE	Thermal-magnetic circuit breaker

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	14 kAIC
VOLTAGE RATING	277V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - GHQ1030
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

