

Specifications



Photo is representative



Eaton HLA3600F

Eaton Classic molded case circuit breaker frame, L-frame, HLA, Frame only, Interchangeable thermal-magnetic trip type, 1250-6000A trip rating, Three-pole, 600A, 600 Vac, 65 kAIC at 240 Vac, 35 kAIC at 600 Vac

General specifications

PRODUCT NAME	Eaton Classic molded case circuit breaker frame
CATALOG NUMBER	HLA3600F
UPC	786679188194
PRODUCT LENGTH/DEPTH	12.9 in
PRODUCT HEIGHT	7.2 in
PRODUCT WIDTH	10.2 in
PRODUCT WEIGHT	15.35 lb
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

AMPERAGE RATING	600 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T207
CIRCUIT BREAKER TYPE	HLA
CIRCUIT BREAKER FRAME TYPE	Frame only
FRAME	L
INTERRUPT RATING	65 kAIC at 240 Vac 35 kAIC at 600 Vac
NUMBER OF POLES	Three-pole
TRIP RATING	1250-6000 A

Resources

CATALOGS	Power Distribution and Control Assemblies, Metering Devices, Protective Relays, Software and Connectivity, Volume 3, Tab 9
MULTIMEDIA	Circuit Breakers Explained
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HLA3600F

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.