

Specifications



Eaton M22-DP-R

Eaton M22 modular pushbutton, M22 Modular Mushroom Pushbutton Operator, 22.5 mm, Momentary, Non-illuminated, Bezel: Silver, Button: Red, IP67, IP69K, NEMA 4X, 13, 5,000,000 Million mechanical operations

General specifications

PRODUCT NAME	Eaton M22 modular pushbutton
CATALOG NUMBER	M22-DP-R
UPC	786685282329
PRODUCT LENGTH/DEPTH	1.44 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	1.44 in
PRODUCT WEIGHT	0.04 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked GoST-R Bureau Veritas
CERTIFICATIONS	CSA Certified CCC Marked Lloyd's Register Certified
CATALOG NOTES	35 mm diameter mushroom head button. Includes contact block mounting adapter.

Product specifications

TYPE	Pushbutton
ACTUATOR COLOR	Red
BEZEL	Silver
ACTUATOR FUNCTION	Momentary
BUTTON COLOR	Red
ACTUATOR	Mushroom
OPERATING MODE	Momentary
ILLUMINATION	Non-illuminated
SERIES	M22
ENVIRONMENTAL RATING	IP67, IP69K
OPERATING CYCLES	5 million
DEGREE OF PROTECTION	NEMA 4X NEMA 13
SIZE	22.5 mm

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - M22-DP-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

