

Specifications

Eaton NZMN4-VE1000-NA



Photo is representative

Eaton Series NZM complete molded case circuit breaker, NZM4-frame, NZMN4, Thermal-magnetic trip, Three-pole, 1000A, 600 Vac, 50 kAIC at 400 Vac, Bolt-on, Selective and generator protection, Rocker lever, motor drive, Front screw, 500-1000A

General specifications

PRODUCT NAME	Eaton Series NZM complete molded case circuit breaker
CATALOG NUMBER	NZMN4-VE1000-NA
UPC	786685631509
PRODUCT LENGTH/DEPTH	8.15 in
PRODUCT HEIGHT	8.27 in
PRODUCT WIDTH	8.27 in
PRODUCT WEIGHT	46.2 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	CSA Certified IEC Rated UL Listed



Powering Business Worldwide

Product specifications

AMPERAGE RATING	1000 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T268
CIRCUIT BREAKER TYPE	NZMN4
TERMINALS	Bolt-on
FRAME	NZM4
CLASS	Selective and generator protection
ACCESSORIES	Rocker lever, motor drive
INTERRUPT RATING	50 kAIC at 400 Vac
CONNECTION	Front screw
OVERLOAD RANGE	500-1000A
NUMBER OF POLES	Three-pole

Resources

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.