

Specifications



Photo is representative



Eaton SVXF15A1-4A1B2

Eaton SVX adjustable frequency drive, 1.5HP, NEMA Type 1/IP21, 480V, FR4, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Varnished Boards

General specifications

PRODUCT NAME	Eaton SVX adjustable frequency drive
CATALOG NUMBER	SVXF15A1-4A1B2
UPC	782116103966
PRODUCT LENGTH/DEPTH	7.5 in
PRODUCT HEIGHT	12.9 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	11 lb
WARRANTY	2 year
CERTIFICATIONS	EN 61800-3 Level H UL 508C IEC 61800-2



Powering Business Worldwide

Product specifications

BRAKE CHOPPER	Brake chopper
MODIFICATION	Varnished Boards
HORSEPOWER	1.50 hp
FRAME SIZE	4
KEYPAD	Alphanumeric
INPUT	EMC H Three-phase
RATING	NEMA 1, IP21
SOFTWARE	Standard

Resources

APPLICATION NOTES	Electromagnetic compatibility (EMC)
CATALOGS	Product Range Catalog Drives Engineering Solid-State Motor Control, Variable Frequency Drives, Volume 6, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SVXF15A1-4A1B2

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.