

## Assembled Limit Switch

E49M11DP1

UPC:782113680941

### Dimensions:

- **Height:** 1.58 IN
- **Length:** 4.27 IN
- **Width:** 2.17 IN

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 250 Vac, 1.5A at 24 Vdc
- **Mounting:** Standard DIN rail
- **Actuator:** Rod lever
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast aluminum
- **Environmental Rating:** IP67
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 1.5A
- **Operating Speed:** 1 mm-2m/s
- **Operating Temperature:** 14° to 176°F
- **Series:** E49

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E49M11DP1](#)

**Certifications:** No Data

**Product compliance:** No Data

