

Eaton 10023PMURF

Catalog Number: 10023PMURF

Eaton LV Unipak capacitor bank, UNIPAK, LV Fixed Capacitor Banks, 240A, 240V, Three-phase, 100 kVAR, Protected, Neon red blown-fuse indicating lights, Three slottedblade-type fuses, NEMA 1, 3R, C2 Frame

General specifications

Product Name	Catalog Number
Eaton LV Unipak capacitor bank	10023PMURF
UPC	Product Length/Depth
782116058525	11.978 in
Product Height	Product Width
36 in	19.3 in
Product Weight	Warranty
104 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	Multiply the 240V kVAR rating by 0.75 to calculate the kVAR value at 208V.



Product specifications

Fuse type

Three slottedblade type fuses with 200,000 ampere interrupting capacity, Fuses mounted on stand-off bushings or fuse blocks, solderless connectors for easy hookup of incoming line conductors.

Product Category

Low Voltage Fixed Capacitor Banks

Enclosure material

14 gauge steel finished with durable powder coat finish

Frame size

C2

Type

UNIPAK

Phase

Three-phase

Rating

100 kVAR

Enclosure

NEMA 1, NEMA 3R

Voltage rating

240V

Amperage Rating

240A

Protection

Three fuses, three lights

Indicators

Red, neon blown-fuse indicating lights are protected by transparent weatherproof guard

Resources

Catalogs

[Eaton's Volume 3—Power Distribution and Control Assemblies](#)

Specifications and datasheets

[Eaton Specification Sheet - 10023PMURF](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)