

# Eaton 100MCSR231

Catalog Number: 100MCSR231

Eaton AUTOVAR 300, Automatic Capacitor Banks, 240A, 240V, Three-phase, 100 kVAR, Wall-mounted, 5 x 20, J Frame, Optional molded-case circuit breaker rated 65 kAIC at 480V and 600V, NEMA 3R weatherproofing.

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton LV AutoVAR 300 capacitor bank	100MCSR231
<b>UPC</b>	<b>Product Length/Depth</b>
786685198163	14 in
<b>Product Height</b>	<b>Product Width</b>
36 in	36 in
<b>Product Weight</b>	<b>Warranty</b>
270 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
CSA Certified UL Listed	Other ratings available, please consult factory.



## Product specifications

### Mounting

Wall

### Product Category

Automatic Capacitor Banks

### Frame size

J

### Options

Optional molded-case circuit breaker rated 65 kAIC at 480V and 600V, NEMA 3R weatherproofing.

### Type

AUTOVAR 300

### Phase

Three-phase

### Rating

100 kVAR

### Voltage rating

240V

### Amperage Rating

240A

### Step X kVAR

5 x 20 kVAR

## Resources

### Catalogs

[Eaton's Volume 3—Power Distribution and Control Assemblies](#)

### Specifications and datasheets

[Low Voltage Power Factor Correction Capacitor Banks and Harmonic Filters](#)

[Eaton Specification Sheet - 100MCSR231](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)